



## C-TEC Disabled Toilet Alarms



C-TEC's Disabled Toilet Alarm kits include everything required for a BS8300 clause compliant emergency assistance alarm (except cables and fixings).

Attractively designed, easy to install and simple to use, it allows a distressed person to raise an alarm in the event of an emergency. To operate, the user simply pulls the cord of a ceiling pull unit to activate a light and sounder outside the WC.

Tried, trusted and respected by users and installers alike, the kits can help building managers and service providers comply with the requirements of BS8300, the Disability Discrimination Act, the Care Standards Act and the English Tourism Council's National Accessibility Scheme.

The kits are also ideal for use as a single zone emergency assistance alarm in changing rooms, solariums, interview rooms and reception areas.

### Features

- Attractive compact design blends perfectly into any sort of decor
- Double gang call controller features a Volt-free relay output, a rotary volume control, Braille text and on-board rechargeable battery backup facility
- Remote reset point c/w sounder provides audible and visual indication of an alarm call inside the WC to reassure users help is on the way
- Simple to install 12 Volt system - four core stranded security cable is ideal for most installations
- All wall-mounting plastic accessories fit 25mm back-boxes, ceiling pull is surface mountable
- Rechargeable back-up battery provides up to 24 hrs stand-by and 15 minutes alarm running time
- System can be easily expanded to include up to three additional conventional call system devices
- Can be used to help building managers and service providers comply with BS8300, the Disability Discrimination Act, the Care Standards Act and the English Tourism Council's National Accessibility Scheme

### Ordering Codes & Information

Cat No	Description
FPA-285	Disabled Toilet Alarm Kit (Plastic)
FPA-286	Disabled Toilet Alarm Kit (Stainless Steel)

\* Kits consists of 1 x call controller c/w onboard battery backup facility, 1 x ceiling pull-cord, 1 x overdoor light c/w sounder, 1 x reset point c/w sounder and 1 x self-adhesive disabled WC label

## Induction Loop Systems



C-TEC's PDA range of induction loop equipment is one of the most comprehensive in the UK. Induction loop systems allow hearing impaired people to hear more clearly. Most hearing aids have a 'T' or 'MT' switch which allows them to pick the electromagnetic field generated by an induction loop system. The hearing aid converts this signal into a sound suited to its user's specific hearing requirements. Any person with a hearing aid positioned within or near the loop can hear the loop signal by switching their hearing aid to the correct position, allowing them to participate more effectively in general conversation and the ordering goods or services.

C-TEC's PDA Range comprises a huge range of amplifiers, microphones, connector plates and test equipment covering virtually every conceivable AFILS application.

### Features

- Ideal for bedrooms, living rooms, TV lounges, studies and other domestic applications
- Simple to adjust, tamper-resistant drive, level, tone and mic. Priority controls
- Input peak, output current, signal present and power on LEDs
- Alert tone input for doorbells, fire alarms, security systems etc
- Automatic compressor limiter
- Fully compliant with EN60118-4 (formerly BS6083) and BS7594:1993

### Ordering Codes & Information

Cat No	Description
FPA-287	Portable Induction Loop Kit - Supplied in a Cardboard Storage/Carry Case
FPA-288	Portable Induction Loop Kit c/w AFILS Tester - Supplied in a Cardboard Storage/Carry Case
FPA-289	Portable Induction Loop Kit - Supplied in a Robust Plastic Storage/Carry Case
FPA-290	Portable Induction Loop Kit c/w AFILS Tester - Supplied in a Robust Plastic Storage/Carry Case
FPA-291	Counter Induction Loop Kit
FPA-292	50m <sup>2</sup> Small Room Loop Kit - Tie/Desk Mic Version
FPA-293	50m <sup>2</sup> TV Lounge Loop Kit - Tie/Desk Mic Version

